

# Halogen non-reflector

## 6899 55W G6.35 24V 1CT

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 - the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

## Product data

#### • General Characteristics

Philips Code 6899 ANSI Code LIF Code G6.35 Cap-Base

**Bulb Material** Quartz-UV Open

Filament Shape Operating Position any Projection Main Application Life to 50% failures 750 hr

#### • Light Technical Characteristics

100 Ra8 Color Rendering

Index

Color Temperature 3000 K Technical

Luminous Flux Lamp 1200 Lm

#### • Electrical Characteristics

Lamp Wattage 55 W 24 V Voltage

# · Luminaire Design Requirements

350 (max) C Pinch Temperature 900 (max) C **Bulb Temperature** 

#### • Product Dimensions

Diameter D 11.5 (max) mm

Light Center Length 29.75 (min), 30 (nom), 30.25 (max)

Pin Diameter P 0.95 (min), 1 (nom), 1.05 (max) mm

Filament Dimensions 4.3x2.0

(WxH) [mm]

# • Product Data

923906220503 Order code 923906220503 Full product code

6899 55W G6.35 24V 1CT Full product name 6899 55W G6.35 24V 1CT/10X10F Order product name

Pieces per pack

Packing configuration 10X10F

100 Packs per outerbox 8711500410122

Bar code on pack -

EAN1 8711500420817

Bar code on intermediate packing -

EAN2

8711500423146 Bar code on

outerbox - EAN3

923906220503 Logistic code(s) -


12NC

Net weight per piece 0.002 kg




# Halogen non-reflector

# Dimensional drawing



# 6899 55W G6.35 24V 1CT

Product	C (Norm)	C (Max)	D (Max)	L (Min)	L (Norm)	L (Max)	P (Min)	P (Norm)	P (Max)
6899 55W G6.35 24V	-	=	11.5	29.75	30	30.25	0.95	1	1.05



G6.35



Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.