

# Charger 24V/DC SLA

MSP-C-AH-00400



## Specifications & order information




<b>Input voltage</b>	100-240 VAC 50-60Hz	<b>Dimensions</b>	330x95x80mm
<b>Input current</b>	700-500mA	<b>Compatible with Arjo number</b>	KTA0101-EU
<b>Output voltage</b>	24 Volt DC	<b>Packaging</b>	Individual, 100 pcs per pallet
<b>Output current</b>	1000mA	<b>M.O.Q.</b>	1 pcs
<b>IP Class charger</b>	IP40	<b>Lead time</b>	2-3 working days
<b>Operational temperature</b>	0°C to +40°C	<b>Article number</b>	MSP-C-AH-00401 for EU MSP-C-AH-00402 for UK MSP-C-AH-00403 for AUS MSP-C-AH-00404 for USA
<b>Storage temperature</b>	-40°C to +70°C	<b>Certification</b>	UL2601-1 IEC60601-1 IEC60335-2-29
<b>Case colour</b>	Blue RAL5007, Black charger	<b>Approval</b>	CE

## 100% compatible

- KTA0102

- MSP-A-AH-00500

## Design enhancements

-  **Safer** by preventing overheating and short circuit
-  **More secure** by preventing battery from moving
-  **Stronger** material



## MDR Compliance

This product complies to MDR (EU) 2017/745 (EU MDR). This product is designed to restore the function off the device without affecting the performance and safety characteristics.

You can use this datasheet as a statement to competent EU authorities.

## Explore more accessories or alternatives in our web shop



**Wall Mounted Charger SLA 24V/DC**  
MSP-C-AH-00200



**Charger SLA 24V/DC Table Model**  
MSP-C-AH-00800



**Battery Pack 24V/DC 6Ah**  
MSP-A-AH-00200