

## PAR 64 Mains Voltage

PAR 64 CP88 240V 500W MFL

### 9061148



#### Range Features

- Pressed glass reflector lamps
- Extremely powerful beam
- Halogen inner capsule, for 100% lumen maintenance through life
- Beam patterns: from very narrow spot through wide angle floods
- Consistency from lamp to lamp
- Instant replaceability without the need to re-focus and re-aim fixtures
- Double internal fused for end of life safety
- Applications
- Theatre lighting
- TV and studio
- Entertainment and Architectural applications
- Displays
- Museums
- Churches
- Towers
- Exhibitions
- Gardens
- Discos



### PRODUCT OVERVIEW

|                          |               |
|--------------------------|---------------|
| Beam angle(°)            | Medium Flood  |
| Colour temperature (K)   | 3200          |
| EAN code                 | 5410288611488 |
| Type                     | PAR 64        |
| Watt (Nominal) (W)       | 500           |
| Ordering number          | 9061148       |
| Average life (Rated) (h) | 300           |

### DATA TABLE

#### Optical data

|                        |              |
|------------------------|--------------|
| Beam angle(°)          | Medium Flood |
| Colour temperature (K) | 3200         |
| Peak intensity (cd)    | 65000        |

#### General data

|                  |               |
|------------------|---------------|
| Burning position | Any           |
| EAN code         | 5410288611488 |
| Type             | PAR 64        |
| Ordering number  | 9061148       |

## PAR 64 Mains Voltage

PAR 64 CP88 240V 500W MFL

### 9061148

|                                 |  |
|---------------------------------|--|
| <b>Range features</b>           | <p>Pressed glass reflector lamps<br/>         Extremely powerful beam<br/>         Halogen inner capsule, for 100% lumen maintenance through life<br/>         Beam patterns: from very narrow spot through wide angle floods<br/>         Consistency from lamp to lamp<br/>         Instant replaceability without the need to re-focus and re-aim fixtures<br/>         Double internal fused for end of life safety</p> <p>Applications</p> <ul style="list-style-type: none"> <li>Theatre lighting</li> <li>TV and studio</li> <li>Entertainment and Architectural applications</li> <li>Displays</li> <li>Museums</li> <li>Churches</li> <li>Towers</li> <li>Exhibitions</li> <li>Gardens</li> <li>Discos</li> </ul> |
| <b>Product name</b>             | PAR 64 CP88 240V 500W MFL  |
| <b>Average life (Rated) (h)</b> | 300  |
| <b>Sales pack quantity</b>      | 6  |
| Electrical data                 |  |
| <b>Watt (Nominal) (W)</b>       | 500  |
| Physical data                   |  |
| <b>Single packaging type</b>    | Box/Sleeve   |
| <b>Weight (kg)</b>              | 0.74   |

## TECHNICAL DRAWINGS

