





## Airfield Conventional Prefocus

	<b>Type 7654H (Halogen)</b> <b>6,6A 45W P28s</b>
	<b>Ordering – No.</b> <b>58320</b>
<b>Product description</b>	Conventional incandescent Airfield Lamp
<b>Features</b>	lamp for constant current regulated series circuits
<b>Applications</b>	Approach lights Threshold lights Runway lights Taxiway lights Obstruction lights

### Technical Details

Rated current (A)	6,6
Wattage (W)	45
Luminous flux (lm)	730
Lumen maintenance	90% after 1500 h
Average lifetime (hours)	2000
Base	P28s
Maximum Overall Length (mm)	max. 98
Bulb Diameter (mm)	max. 33
Light center length (mm)	38,0
Filament Type	C-8
Burning Position	S
Chromaticity	Within white boundaries
Packaging quantity	20
Environmental remark	Product don't contain lead or mercury and is conform with Directive 2011/65/EC "Restriction of the use of certain hazardous substances in electrical and electronic equipment".

### Drawing (in mm)



valid from	05.03.2014—V2—PN14/0072
replace for	30.01.2013—V1
file	58320.100.pdf