

9-Pin D-sub terminal connector modular



2010C246 - Male connector with locking screw connection



2010C247 - Female connector with locking screw connection



2010C248 - Male connector with jackscrew nut connection





2010C249 - Female connector with jackscrew nut connection

Included accessories
 1x Screw driver
 1x Cable strain Relief
 2x Fastening screw



Material:
 Housing: PP
 Connector insulator: PBT+30%GF (UL94V-0)
 Contact: Brass
 Contact plated: Nickel
 Connector shell plated: Cu60µ/Ni100-120µ
 Technical:
 Contact current rating: 5A max.
 Insulation resistance: 1000MΩ min. at 500V/DC
 Dielectric withstanding voltage: 500V/AC(R.M.S)/1min.
 Operation temperature: -20 ~85°C



- 1 DCD (Data Carrier Detect)
- 2 RXD (Received Data)
- 3 TXD (Trasmitted Data)
- 4 DTR (Rata Terminal Ready)
- 5 GND (Signal Ground)
- 6 DSR (Data Send Ready)
- 7 RTS (Request to Send)
- 8 CTS (Clear to Send)
- 9 RI (Ring Indicator)