


859619F-1



BUSHING FINISH:	SILVER
LEAD FINISH:	SILVER
CAPACITANCE	1000pF +200%
TEMP. RANGE	-25°C TO +85°C
CURRENT	15 AMP MAX.
WORKING VOLTAGE	85°C 100 VDC
DC RESISTANCE	.01 Ohms MAX.
I.L. = NO LOAD	
25MHZ	10dB
100MHZ	20dB
500MHZ	50dB
1GHZ	55dB
SCHEMATIC	
MARKING:	
PART:	S619F1
BAG:	
PACK:	SCI 859619F-1
DATE CODE	
LDT No.	
QTY/BAG	(200/BAG MAX.)

NOTES:

1. MAX. INSTALLATION TORQUE = 4in-lbs.
2. HARDWARE IS NOT INCLUDED.
3. RECOMMENDED MOUNTING: ø.177±.002 [4.50±1.05] HOLE
4. THIS IS A LEAD FREE PRODUCT.
5. MAX. REFLOW IS 245°C FOR 5 SEC.