

TABLE MAT KIT
32-290-600x

Double layer table mat with a dissipative top-layer and a conductive bottom layer

Physical properties

Abrasion resistance: $\leq 200 \text{ mm}^3$ (ISO 4649, Method A)
 Hardness: 75 Shore A +/-5 (ISO 7619)
 Residual indentation: $\leq 0.2 \text{ mm}$ (EN 433)
 Thickness: 2.0 mm

Electrical properties

Resistant to ground: $\leq 10^9 \Omega$
 Surface resistance: $\leq 1.0 \times 10^9 \Omega$
 Compliant to: IEC 61340-5-1


Dimensions, Features and Part Number

Part Number	Description	Dimensions	Colour
32-290-6000	1,5 m cord with Euro plug	60x90 mm	Blue
32-290-6001	2,5 m cord with CH plug	60x90 mm	Blue

Supplied with 2 x 10mm male studs, coli cord 7-10 mm female (ref 30-560-0671), wrist strap fabric 7 mm male (ref 30-560-0007), grounding plug 10 mm female Euro or CH.