


MIRO TR 90-250VAC SK OPTO-COUPLER MODULE


IN: 250 VAC - OUT: 48 VDC / 2 A

Transistor 2 A
230 V AC
Screw terminals

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Voltage range ON	90...250 V AC
Voltage range OFF	0...30 V AC
Control current	15 mA
LED display	LED (yellow)

General data

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	78×6.2×65 mm

Output

Switching voltage	5...48 V DC
Switching current per output	1 mA...2 A (without derating)
Saturation voltage (across output)	max. 0.3 V DC
Leakage current (output is open)	max. 0.3 mA
Switching frequency	max. 10/1 Hz (resist./ind.)
Switching time ON/OFF	3/10 ms

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1