



**M12 MALE ON TOP OF MSUD VALVE PLUG FORM BI 11MM**

Form BI (11 mm) – M12, connector top entry  
LED (yellow)  
3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image

### Approvals



### Form

42001

### Technical Data

Operating voltage	24 V AC/DC $\pm 25\%$
Operating current per contact	max. 4 A
Configuration	2 contacts + PE
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	M3/M12 $\times$ 1 mm (recommended torque 0.4/0.6 Nm)

### General data

Temperature range	-25...+85 °C
-------------------	--------------

### Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1