

## horizontal clamp with variable clamping height

with open clamping arm and horizontal base



### Application:

Quick-action clamp with infinitely adjustable balancing function for workpieces with different clamping widths.

### Version:

- galvanised and passivated.
- ergonomic, oil-resistant handle with large hand rest and soft components.
- protection against the loss of the clamping screw on the end of the clamping arm. complete with zinc-plated clamping bolt
- Size 20 clamping bolt M6 x 40 mm
- Size 50 clamping bolt M8 x 39 mm
- Size 70 clamping bolt M8 x 55 mm

### Advantage:

- variable clamping height, for clamping different workpieces
- used for small lot sizes
- infinitely adjustable clamping force
- ergonomic 2 component handle
- protection against loss on clamping arm



<b>Art. no.</b>	<b>26215 017</b>
<b>Size</b>	70
<b>Distance</b>	8.5 mm
<b>Basic length</b>	104 mm
<b>Elongated hole spacing</b>	25.4 mm
<b>Hole distance 2</b>	25.4 mm
<b>Drill hole</b>	6.5 mm
<b>Drill hole 2</b>	6.5 mm
<b>Length 2</b>	35 mm
<b>Length 3</b>	50 mm
<b>Height</b>	41 mm
<b>Overall height of lower handle</b>	90 mm
<b>Overall height of upper handle</b>	174 mm
<b>Max. adjustment range</b>	19.7 mm
<b>Min. adjustment range</b>	-6.6 mm
<b>Thickness</b>	13 mm
<b>Distance 2</b>	6.3 mm
<b>Base plate length 2</b>	12.7 mm
<b>Length</b>	261 mm
<b>Min./max. elongated hole spacing</b>	32-44 mm
<b>Hole distance</b>	25.4 mm
<b>Base plate width</b>	57 mm
<b>Base plate length</b>	63.5 mm
<b>Height 2</b>	35 mm
<b>Height 3</b>	60 mm

### EAN-Code

4020772021979