

META CLIP boltless rack with shelves

Load capacity per bay 100/230 kg, plastic coated



Application:

Universal rack system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools.

Execution:

- Double-row boltless rack with pre-assembled frame = clinched frame
- Both rows securely connected on the back
- Shelves height-adjustable, spacing 25 mm
- Shelves with a 50 mm hole grid to accommodate accessories
- Basic rack planning dimensions: Nominal length + 56 mm, 2 x nominal depth + 75 mm

Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



| | |
|---|------------------|
| Art. no. | 50167 498 |
| Brand | META |
| Manufacturer Part Number | 200176594 |
| Height | 2000 mm |
| Length | 1006 mm |
| Depth | 636 mm |
| Nominal length | 1000 mm |
| Nominal depth | 600 mm |
| Design | Add-on shelving |
| Type of assembly | To insert |
| Surface | Plastic-coated |
| Design of the frame | Pre-assembled |
| Grid dimension | 25 mm |
| Number of shelves | 5 PCS |
| Load-carrying capacity per shelf | 150 kg |
| Load-carrying capacity per field | 1650 kg |
| Number of frame | 1 PCS |
| Quality label | RAL-RG 614/1 |
| Made in | Germany |
| Gross Weight | 56.517 kg |
| Product Group | 508 |

EAN

4026212282108