

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Jigsaw Blades
Catalogue number	865A, 865B, 865C, 865D, 865H, 865L, 865P, 865R, 865T, 865W, 865X & 865Y
Date	23/01/2015

Range Description

A range of professional quality Jigsaw blades

Features

- Professional quality Chrome Vanadium blades for strength and durability
- Multipurpose blade and blades for cutting metal are of Bi-metal construction for shatter free cutting



865A



865B



865C



865D



865H




865L



865P



865R




865T



865W



865X



865Y

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T0865A	Jigsaw Blade 865A Card of 5	5013969135008	82029919	1
T0865B	Jigsaw Blade 865B Card of 5	5013969135107	82029919	1
T0865C	Jigsaw Blade 865C Card of 5	5013969135206	82029919	1
T0865D	Jigsaw Blade 865D Card of 5	5013969135305	82029919	1
T0865H	Jigsaw Blade 865H Card of 5	5013969135503	82029919	1
T0865L	Jigsaw Blade 865L Card of 5	5013969135701	82029919	1
T0865P	Jigsaw Blade 865P Card of 5	5013969053050	82029919	1
T0865R	Jigsaw Blade 865R Card of 5	5013969135800	82029919	1
T0865T	Jigsaw Blade 865T Card of 5	5013969135909	82029919	1
T0865W	Jigsaw Blade 865W Card of 5	5013969703672	82029919	1
T0865X	Jigsaw Blade 865X Card of 5	5013969703689	82029919	1
T0865Y	Jigsaw Blade 865Y Card of 5	5013969703771	82029919	1

Technical product information	<p>Bosch bayonet type fitting Suitable for a wide range of manufacturers jigsaws including: AEG, Bosch, De-Walt, Elu, Festo, Milwaukee, Holzher, Maakita, Metabo, Skil....</p>																																																																																	
	<p>Cutting capacities</p> <table border="1"> <thead> <tr> <th>Item</th> <th>Application</th> <th>Cut Thickness</th> <th>Blade length</th> <th>Tooth Pitch</th> <th>Bosch equivalent</th> </tr> </thead> <tbody> <tr> <td>T0865A</td> <td>Metal thin</td> <td>1.5-3mm</td> <td>50mm</td> <td>1.2mm</td> <td>T118A</td> </tr> <tr> <td>T0865B</td> <td>Wood coarse</td> <td>5-60mm</td> <td>75mm</td> <td>3mm</td> <td>T111C</td> </tr> <tr> <td>T0865C</td> <td>Wood clean straight</td> <td>4-30mm</td> <td>75mm</td> <td>2.5mm</td> <td>T101B</td> </tr> <tr> <td>T0865D</td> <td>Wood fast coarse</td> <td>8-60mm</td> <td>75mm</td> <td>4mm</td> <td>T144D</td> </tr> <tr> <td>T0865H</td> <td>Metal medium thick</td> <td>3-6mm</td> <td>50mm</td> <td>2mm</td> <td>T118B</td> </tr> <tr> <td>T0865L</td> <td>Wood fine</td> <td>6-60mm</td> <td>75mm</td> <td>4mm</td> <td>T101D</td> </tr> <tr> <td>T0865P</td> <td>Wood clean deep straight</td> <td>8-75mm</td> <td>95mm</td> <td>4mm</td> <td>T301D</td> </tr> <tr> <td>T0865R</td> <td>laminare clean (down cut)</td> <td>4-30mm</td> <td>75mm</td> <td>2.5mm</td> <td>T101BR</td> </tr> <tr> <td>T0865T</td> <td>Wood fast coarse curved</td> <td>8-60mm</td> <td>75mm</td> <td>4mm</td> <td>T244D</td> </tr> <tr> <td>T0865W</td> <td>Universal multi-material</td> <td>3-100mm</td> <td>110mm</td> <td>7.8-2.5mm</td> <td>-</td> </tr> <tr> <td>T0865X</td> <td>Wood fast coarse straigh (double cut)</td> <td>3-60mm</td> <td>75mm</td> <td>2mm</td> <td>T118B</td> </tr> <tr> <td>T0865Y</td> <td>Metal multipurpose</td> <td>1.5-3mm Metal 1.5-65mm composites</td> <td>110mm</td> <td>1.2mm</td> <td>T318A</td> </tr> </tbody> </table>					Item	Application	Cut Thickness	Blade length	Tooth Pitch	Bosch equivalent	T0865A	Metal thin	1.5-3mm	50mm	1.2mm	T118A	T0865B	Wood coarse	5-60mm	75mm	3mm	T111C	T0865C	Wood clean straight	4-30mm	75mm	2.5mm	T101B	T0865D	Wood fast coarse	8-60mm	75mm	4mm	T144D	T0865H	Metal medium thick	3-6mm	50mm	2mm	T118B	T0865L	Wood fine	6-60mm	75mm	4mm	T101D	T0865P	Wood clean deep straight	8-75mm	95mm	4mm	T301D	T0865R	laminare clean (down cut)	4-30mm	75mm	2.5mm	T101BR	T0865T	Wood fast coarse curved	8-60mm	75mm	4mm	T244D	T0865W	Universal multi-material	3-100mm	110mm	7.8-2.5mm	-	T0865X	Wood fast coarse straigh (double cut)	3-60mm	75mm	2mm	T118B	T0865Y	Metal multipurpose	1.5-3mm Metal 1.5-65mm composites	110mm	1.2mm
Item	Application	Cut Thickness	Blade length	Tooth Pitch	Bosch equivalent																																																																													
T0865A	Metal thin	1.5-3mm	50mm	1.2mm	T118A																																																																													
T0865B	Wood coarse	5-60mm	75mm	3mm	T111C																																																																													
T0865C	Wood clean straight	4-30mm	75mm	2.5mm	T101B																																																																													
T0865D	Wood fast coarse	8-60mm	75mm	4mm	T144D																																																																													
T0865H	Metal medium thick	3-6mm	50mm	2mm	T118B																																																																													
T0865L	Wood fine	6-60mm	75mm	4mm	T101D																																																																													
T0865P	Wood clean deep straight	8-75mm	95mm	4mm	T301D																																																																													
T0865R	laminare clean (down cut)	4-30mm	75mm	2.5mm	T101BR																																																																													
T0865T	Wood fast coarse curved	8-60mm	75mm	4mm	T244D																																																																													
T0865W	Universal multi-material	3-100mm	110mm	7.8-2.5mm	-																																																																													
T0865X	Wood fast coarse straigh (double cut)	3-60mm	75mm	2mm	T118B																																																																													
T0865Y	Metal multipurpose	1.5-3mm Metal 1.5-65mm composites	110mm	1.2mm	T318A																																																																													

	Item	hard and softwood	laminated particle board	Plywood	Glued wood	Chipboard	Plastic	Metal	Wood & nails	Non ferrous metal	Aluminium
	T0865A							Y		Y	Y
	T0865B	Y	Y	Y	Y	Y	Y				
	T0865C	Y	Y	Y	Y	Y	Y				
	T0865D	Y	Y	Y	Y	Y	Y				
	T0865H							Y		Y	Y
	T0865L	Y	Y	Y	Y	Y	Y				
	T0865P	Y	Y	Y	Y	Y	Y				
	T0865R	Y	Y	Y	Y	Y	Y				
	T0865T	Y	Y	Y	Y	Y	Y				
	T0865W	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
	T0865X	Y	Y	Y	Y	Y	Y				
	T0865Y							Y		Y	Y
Standards compliance	None applicable										
User health and safety information	None applicable										
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations										
Material safety data	None applicable										
Warranty	C.K Jigsaw blades are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered										
Country of origin	Germany										

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T0865A	9	2	75	5	100	3	185	35
T0865B	9	2	100	6	100	3	185	38
T0865C	9	2	100	6	100	3	185	38
T0865D	9	2	100	6	100	3	185	38
T0865H	9	2	75	5	100	3	185	35
T0865L	9	2	100	6	100	3	185	38
T0865P	9	2	115	7	100	3	185	43
T0865R	9	2	100	6	100	3	185	38
T0865T	9	2	100	6	100	3	185	38
T0865W	9	2	132	8	100	3	217	52

T0865X	9	2	100	6	100	3	185	38
T0865Y	9	2	132	8	100	3	217	52

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T0865A	-	-	-	-		
T0865B	-	-	-	-		
T0865C	-	-	-	-		
T0865D	-	-	-	-		
T0865H	-	-	-	-		
T0865L	-	-	-	-		
T0865P	-	-	-	-		
T0865R	-	-	-	-		
T0865T	-	-	-	-		
T0865W	-	-	-	-		
T0865X	-	-	-	-		
T0865Y	-	-	-	-		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T0865A	1	Blister	7	Backing card	-	-	-	-
T0865B	1	Blister	7	Backing card	-	-	-	-
T0865C	1	Blister	7	Backing card	-	-	-	-
T0865D	1	Blister	7	Backing card	-	-	-	-
T0865H	1	Blister	7	Backing card	-	-	-	-
T0865L	1	Blister	7	Backing card	-	-	-	-
T0865P	1	Blister	7	Backing card	-	-	-	-
T0865R	1	Blister	7	Backing card	-	-	-	-
T0865T	1	Blister	7	Backing card	-	-	-	-
T0865W	2	Blister	10	Backing card	-	-	-	-
T0865X	1	Blister	7	Backing card	-	-	-	-

T0865Y	2	Blister	10	Backing card	-	-	-	-
--------	---	---------	----	-----------------	---	---	---	---