


GDME LG 230

Industrial Connectors:Rectangular connectors GDM-series:Type AEN 175301-803 (DIN 43650) / ISO 4400:Electronic inserts for GDME

Product description	
Description	function indicator (glow lamp)
Type	GDME LG 230
Order No.	831 824-001
Standard	DIN EN 175 301-803-A
Construction type	A
Description of Wiring	
LED color	glow lamp
Drawing	



Technical data	
Rated voltage	AC/DC 250 V
Rated current	8 A
Environmental conditions	
Temperature range	-40 °C to +110 °C
Packing unit	
Packaging unit	50 pieces