

**VPMS Ex (ex blanking plug, brass)
VP M20 EXE MS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP M20 EXE MS
Order No.	1210900000
Version	VPMS Ex (ex blanking plug, brass), Blanking plug, M 20, 12 mm, Brass, nickel-plated
GTIN (EAN)	4032248992263
Qty.	50 pc(s).

Data sheet

**VPMS Ex (ex blanking plug, brass)
VP M20 EXE MS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	15 mm	Length (inches)	0.591 inch
Net weight	30.52 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1; 96-45-7 Imidazolidine-2-thione
------------	---

General information

Material	Brass, nickel-plated	External thread	M 20
Pitch of thread	1.5 mm	Length of thread	12 mm
AF size 1	23 mm	Protection degree	IP54, IP64, IP68
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
O-Ring	NBR	Torque for cap nut, min.	4.6 Nm
Torque for cap nut, max.	6.9 Nm	Torque for connecting adapter, min.	11.5 Nm
Torque for connecting adapter, max.	23 Nm		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-35
eClass 10.0	27-14-44-25		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**VPMS Ex (ex blanking plug, brass)
VP M20 EXE MS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

