



Model Number


ML17-54/115b/120

Retroreflective sensor with fixed cable and M12 connector, 4-pin


Features

- Compact series in universal housing for standard applications
- · Miniature design
- Front mounting with M18-threads or side mounting holes
- 360° high visibility LEDs
- Time-saving mounting with quick clamp system
- Version with polarized filters detect shiny objects

Dimensions



Electrical connection




- O = Light on
- = Dark on

Pinout




Indicators/operating means



1	Signal display	yellow
2	Operating display	green
3	Sensitivity adjustment	

Technical data General specifications Effective detection range 0 ... 3.5 m Reflector distance 50 ... 3500 mm Threshold detection range 5 m FE-RR1 reflector Reference target LED Light source Light type modulated visible red light, 626 nm Polarization filter Ambient light limit ≤ 10000 Lux Indicators/operating means Operation indicator LED green Function indicator LED yellow, lights up with receiver lit Control elements sensitivity adjustment **Electrical specifications** 10 ... 30 V DC, class 2 Operating voltage U_B max. 10 % Ripple < 25 mA No-load supply current I_0 Operating current 100 mA max per output Time delay before availability t_v ≤ 200 ms Output Switching type light/dark on Signal output 2 PNP, short-circuit protected, reverse polarity protected, open collectors max. 30 V DC Switching voltage Switching current max. 100 mA U_d Voltage drop ≤ 2 V DC Switching frequency 500 Hz Response time < 1 ms **Ambient conditions** Ambient temperature -20 ... 55 °C (-4 ... 131 °F) -40 ... 75 °C (-40 ... 167 °F) Storage temperature Mechanical specifications Degree of protection IP67 Connection fixed cable 150 mm with M12 x 1 male connector, 4 pin Material Housing ABS Optical face Acrylic approx. 23 g Compliance with standards and directi-Standard conformity Product standard EN 60947-5-2:2007 IEC 60947-5-2:2007 Approvals and certificates **UL** approval cULus CCC approval CCC approval / marking not required for products rated ≤36 V

Curves/Diagrams



Accessories

OMH-ML17-EZ
Mounting bracket

OMH-ML17

Mounting bracket

OMH-ML17-1 Mounting bracket

Other suitable accessories can be found at www.pepperl-fuchs.com



