

Accessory

PICO-LPG-635-660
Order Number: 70140354

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-50		85	°C
Storage Temperature	-50		80	°C

Technical Parameters

RoHS yes

Optical Parameters

Luminous transmittance	20.00 %
LB Rating	630-711 DIR LB5, 648-708 D LB5 + IR LB6, 651-704 D LB5 + IR LB7, 654-699 D LB5 + IR LB8, 712-713 DIR LB4, 714-717 DIR LB3
Lens Color	Aqua

Mechanical Parameters

Size	144x145x50 mm
Material	Polymer
Housing Color	black
Weight	10 g

(*) Over the complete operating temperature range

Features




- Complete protection
- Comfortable fit over prescription glasses or alone
- Adjustable temples and Side-shields for wide field of view
- CE Certified EN 207
- With Picotronic Logo imprint

Picture



Safety Label



Valid Revision

| 12-FEB-2021