

Identification

Part No.


Pg

Drawing

Dimensions in mm

## Special cable clamp

thermoplastic, with bell-mouth cable fitting and strain relief



09 00 000 5165  
09 00 000 5166  
09 00 000 5167  
09 00 000 5168  
09 00 000 5169  
09 00 000 5170

11  
13,5  
16  
21  
29  
36

a	c	D	d		e	SW	f	Pg
			min.	max.				
35	M3	33	6	11	9	19	35	11
36,5	M3	36	7,5	14	10	22	39	13,5
40	M4	38	10	16	10	24	45	16
47,5	M4	46	12,5	21	12	30	51	21
55,5	M5	60	17	29	13	41	64	29
62	M5	76	20,5	36	13	50	72	36

## Special cable clamp


metal, with bell-mouth cable fitting and strain relief

for Standard Hoods/Housings




09 00 000 5101 ✓  
09 00 000 5102 ✓  
09 00 000 5103 ✓  
09 00 000 5104 ✓  
09 00 000 5106

11  
13,5  
16  
21  
29



a	b	c	D	d		e	SW	Pg
				min.	max.			
26,6	4	M3	23	6	11	9	19	11
31	4	M3	28	9	14	10	22	13,5
33	5	M4	30	10	16	9,5	24	16
39,5	7	M4	37	13,5	21	12	30	21
49	8	M5	50	19	29	13	41	29


for Hoods/Housings Han M



09 37 000 5101  
09 37 000 5102  
09 37 000 5103  
09 37 000 5104  
09 37 000 5106

11  
13,5  
16  
21  
29

for Hoods/Housings Han U



09 36 000 5101  
09 36 000 5102  
09 36 000 5103  
09 36 000 5104  
09 36 000 5106 ✓

11  
13,5  
16  
21  
29

## Normal seal

for Standard Hoods/Housings



09 00 000 5020  
09 00 000 5021  
09 00 000 5022  
09 00 000 5023  
09 00 000 5024  
09 00 000 5025  
09 00 000 5026

11  
13,5  
16  
21  
29  
36  
42

for Hoods/Housings Han M



09 37 000 5020  
09 37 000 5021  
09 37 000 5022  
09 37 000 5023  
09 37 000 5024

11  
13,5  
16  
21  
29

∅

11  
13  
15  
20  
29  
36  
42

