


Product Bulletin PB00179





Belden Speaker cables use OFHC conductors offer Top Performance.

Top range of speaker cables complying to the CPR Euroclass requirements up to B2ca.



Belden LSZH OFHC Speaker cables answer the need for an CPR Euroclass rated, high-end speaker cable with distinct performance and installation benefits.



## **Enhanced Sound Performance**

The copper conductors of Brilliance Low Cap OFHC Speaker cable have been manufactured using an upright shaft manufacturing process. The result of this process is a highconductivity copper conductor that is inherently free of impurities.

## **Construction details**

The range of products consists of 2 x 1.5 mm2, 2 x 2.5mm2, 4 x 2.5mm2 and 2 x 4.0 mm2. These are available in CPR Euroclass ratings:

- B2ca-s1,d1,a1
- Cca-s1,d1,a1
- Dca-s2,d2,a1



## **Euroclass program**

Euroclasses are uniform assessment methods or classifications that reflect real-life environments for building products based on reaction-to-fire performance. Based on the cable's performance, it is placed into the Euroclass system that indicates its behavior during a fire.

The Euroclass program provides rankings based on the following criteria:

- Contribution to expanding a fire (rating from "no contribution" to "high contribution," with several levels in between)
- Smoke production development (rating from "limited production" to "strong production")
- Burning falling particles/droplets (rating from "no" to "high")
- Class corrosiveness/acidity of combustion gases (ranging from "low corrosiveness" to "high corrosiveness")





Description	Part No.	Euroclass	No. of Cond.	Standard Lengths [m]	Standard Weight [kg]	Diameter over Insulation [mm]	DC Resistance conductor [Ω/km]	Nominal O.D. [mm]
1.5 mm2 Stranded			Oxygen-fr	ee Bare Copper	Conductors Ca	bles		
LSZH Insulation	LSZH Jacket	t						
Red and Black cores	70045	Dca-s2,d2,a1	2	100	62.1	2.3	< 13	6.3
				250				
				500				
	70045LW	Cca-s1,d1,a1	2	100	72.6	2.3	< 13	6.8
				250				
				500				
	70045LV	B2ca-s1,d1,a1	2	100	72.6	2.3	< 13	6.8
				250				
				500				
2.5 mm2 Stranded			Oxygen-fr	ee Bare Copper	Conductors Ca	bles		
LSZH Insulation	LSZH Jacket	t 						
Red and Black cores	70046	Dca-s2,d2,a1	2	100		2.7	< 8	7.3
				250				
			-	500				
	70046LW	Cca-s1,d1,a1	2	100		2.7	< 8	8
				250				
				500				
	70046LV	B2ca-s1,d1,a1	2	100		2.7	< 8	8
				250		-		
				500				
	70047	Dca-s2,d2,a1	4	100		2.7	< 8	8.5
				250				-
				500				
	70047LW	Cca-s1,d1,a1	4	100		2.7	< 8	9.5
				250				
				500				
	70047LV	B2ca-s1,d1,a1	4	100		2.7	< 8	9.5
				250				
4 0 0:	(FO . O O	0		500				
4 mm2 Stranded ( LSZH Insulation		•	xygen-free	Bare Copper   Co	onductors Cable	S		
Red and Black								
cores	70048	Dca-s2,d2,a1	2	100		3.3	< 4.5	8.6
				250				
				500			. =	
	70048LW	Cca-s1,d1,a1	2	100		3.3	< 4.5	8.6
				250				
				500				
	70048LV	B2ca-s1,d1,a1	2	100		3.3	< 4.5	8.6
				250				

500

