



### Main

|                           |                                    |
|---------------------------|------------------------------------|
| Product or component type | Uninterruptible power supply (UPS) |
| Mounting support          | Wall<br>Floor                      |
| Reset                     | Automatic reset                    |
| Topology                  | Line interactive                   |

### Complementary

|                         |   |
|-------------------------|---|
| Type of installation    | Indoor  |
| Surge Energy            | 156 J   |
| Type of signal          | Stepped approximation to a sinewave   |
| Protection device type  | Surge protection device (SPD)<br>Miniature circuit breaker (MCB)<br>Fuse  |
| Input voltage           | 230 V AC  |
| Output voltage          | 230 V AC  |
| IP degree of protection | IP20  |
| Transfer time           | 6 ms  |
| Network frequency       | 45...65 Hz  |
| Power range             | 1000 VA<br>600 W  |
| Electrical connection   | Input: 1 inlet IEC 320 C14<br>Output: 6 outlet IEC 320 C13  |
| Local signalling        | Alarm, distinctive for low battery<br>Alarm, continuous or intermittent tone for overload<br>LED for battery status |
| Battery type            | Lead-acid battery   |
| Number of batteries     | 1   |
| Charging time           | 8 h   |
| Battery voltage         | 12 V  |
| Battery life            | 5 year(s)   |
| Quantity per set        | Set of 1  |
| Net weight              | 5.7 kg  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|        |          |
|--------|----------|
| Height | 92.5 mm  |
| Width  | 160.5 mm |
| Depth  | 305 mm   |

### Environment

|                                       |                          |
|---------------------------------------|--------------------------|
| Relative humidity                     | 0...90 %, non-condensing |
| Operating altitude                    | 0...6561 ft              |
| Ambient air temperature for operation | 0...40 °C                |
| Product certifications                | CE                       |

### Packing Units

|                              |                |
|------------------------------|----------------|
| Unit Type of Package 1       | PCE            |
| Number of Units in Package 1 | 1              |
| Package 1 Weight             | 5.897 kg       |
| Package 1 Height             | 30.505 cm      |
| Package 1 width              | 16.51 cm       |
| Package 1 Length             | 9.246 cm       |
| SCC14                        | 10731304338380 |

### Contractual warranty

|          |         |
|----------|---------|
| Warranty | 2 years |
|----------|---------|