

Global Trac Pulse

GLOBAL TRAC PULSE 3M WHITE

XTSC6300-3



Product features

- Global Trac Pulse - 3 Circuit Track 16A/400V, circuits can be controlled individually, control 2 Circuit 1A/50V FELV AC, DALI (FELV), DMX, LON, EIB, 1-10 V etc. compatible., aluminum body, suitable for surface mounting, 3000 x 31.5 x 32.5 mm (L x W x H), 2.600 kg, white (RAL 9010).



PRODUCT OVERVIEW

Product name	GLOBAL TRAC PULSE 3M WHITE
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC000101
Warranty	5 years
Light colour	N/A
Dimmable	Yes
Housing colour	RAL 9010 - Pure white
IP rating	IP20
IK rating	IK02
Product EAN number	6410014531539

DATA TABLE

General data

Product name	GLOBAL TRAC PULSE 3M WHITE
Technology	Accessory
Housing	Aluminium
General application	Retail
Operating temperature range (°C)	0°C...+25°C
ETIM Class	EC000101
Warranty	5 years

Optical data

Light colour	N/A
--------------	-----

Electrical data

Mains voltage (V)	220-240V
Dimmable	Yes

Physical data

Housing colour	RAL 9010 - Pure white
IP rating	IP20

Global Trac Pulse GLOBAL TRAC PULSE 3M WHITE XTSC6300-3

IK rating	IK02
Nominal Product Length (mm)	3000
Nominal Product Width (mm)	31.5
Nominal Product Height (mm)	32.5
Cutout Dimensions (W x L in mm or Diameter in mm)	3000
Weight (kg)	2.6

Packaging

Single packaging type	Carton
Product EAN number	6410014531539
Packaging single length / height (cm)	300.0
Packaging single width (cm)	3.15
Packaging single depth (cm)	3.25
DUN14 (outer)	06410014531539
Units per outer package	4
Packaging outer length / height (cm)	300.0
Packaging outer width (cm)	12.8
Packaging outer depth (cm)	3.6

Safety data

Optimal operating condition (°C)	0-25
Special purpose lamp	No
Dry applications use only	Yes