

Reducing sleeves E1 + E2 with slot

With groove

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground



Art. no.	22778 230
Brand	ORION
Manufacturer Part Number	22778230
Clamping diameter	20 mm
Clamping diameter 2	12 mm
Collar diameter	25 mm
Length	52 mm
Collar width	3 mm
Clearance	3.5 mm
Length 2	45.5 mm
Groove width	13 mm
Gross Weight	0.095 kg
Product Group	2AL

EAN

4053625466092