

Cordless combination hammer drill

CHE 18.0-EC

FLEX

Version:

- Brushless motor with higher efficiency and longer service life
- Function switch with four functions: drilling, hammer drilling, chiselling, chisel adjustment
- Electronic Management System (EMS) protects the machine, prolongs its life and increases efficiency
- Rotation stop for chipping
- Robust high-pressure die-cast aluminium gear housing
- With throttle switch and continuous operation function
- Electronic rapid acting brake
- Twist-proof additional handle with depth stop
- Integrated LED light with after-glow function
- LED battery capacity display



Art. no.	71030 104
Model	CHE 18.0-EC
Manufacturer Article Number	461.768
Battery voltage	18 V
Battery included	Yes
Type of rechargeable battery/battery	Li-Ion
Rechargeable battery/battery capacity	5 Ah
Number of rechargeable batteries/batteries	2 PCS
Max. drilling diameter in wood	20 mm
Max. drilling diameter in steel	13 mm
Min./max. idle speed	0-1400 rpm
Min./max. idle impact rate	0-4500 rpm
Suitable for tool holding device	SDS-plus
Length x width x height	280 x 75 x 220 mm
Included in delivery	Handle, depth stop, 2x 5 AH batteries, quick charger, transport case, case insert
Max. drilling diameter in concrete	18 mm

EAN-Code

4030293230675