

digital current clamp multimeters

TRUE RMS

BENNING

Application:

Measurements in industrial, electro-technical and photovoltaic sectors

Execution:

- Automatic function and measuring range selection
- Measurement errors due to selecting the incorrect measuring range are ruled out
- functions: LoZ, ZERO

Delivery:

Includes Accessories: bag, batteries, measuring leads



Art. no.	75024 411
Brand	BENNING
Manufacturer Part Number	044066
Model	CM 5-1
Display range	9999 digits
Measuring accuracy	+/- 2 %
Min./max. test voltage (DC)	0.7 V/DC-1000 V/DC
Min./max. test voltage (AC)	1.3 V/AC-750 V/AC
Min./max. alternating current of measuring range	0.9 A-600 A
Min./max. direct current of measuring range	0.9 A-600 A
Continuity testing	Yes
Diode testing	Yes
Min./max. electrical-resistance measuring range	1 Ohm-10 kOhm
Volt sensor	No
Max. collet opening	35 mm
Memory function	HOLD, ZERO
Measuring procedure	TRUE RMS
Overvoltage protection category	CAT III/1000 V, CAT IV/600 V
Length x width x height	215 x 85 x 51 mm
Gross Weight	0.640 kg
Product Group	7AH

EAN

4014651440661