

Data Sheet

YV Jumper wire 1 x0.2 mm², 25 meter, Green



Photo just for reference.

Strand per conductor:	0.2 mm ²
No. of conductors:	1 x 0.5 mm
Length:	25 meter
Color:	Green
Rated voltage:	48V
Rated current:	1.6A
Jacket, outer dimension:	PVC 1.1 mm
Conductor material:	Tinned-copper
Conductor structure:	one core
Insulation material (with thickness):	PVC 0.3 mm
Core diameter:	0.5mm
Insulation resistance:	Min 200M ohm x km
Conductor resistance:	Max 110Ω/KM
Maximum dielectric strength:	800V / AC
Temperature range:	-20 to +70°C