



Full Moon

FULL MOON OPAL TUTTOSCH 24W 4K

Order code **75333**

EAN **8002219866592**

Technical specifications

Absorbed Power	24 W
Supply voltage type	AC
Nominal voltage (AC)	230 Vac
Ambient temperature (min)	-20 °C
Ambient temperature (max)	40 °C
Insulation class	II
CCT light tone	4000 K
Photobiological risk	RG0
CRI color rendering	>80
Diameter	380 mm
Efficiency	80 lm/W
Frequency (max)	60 Hz
Frequency (min)	50 Hz
Power factor	0.5
Glow wire strength	650 °C - 30s.
Luminaire flux	1920 lm
Voltage supply range (max)	265 V
Voltage supply range (min)	180 V

Mechanical specifications

Height	90 mm
Weight	0.69 Kg
Protection grade IP	IP44
Protection grade IK	IK03

Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN IEC 60598-1:2021, EN 60598-2-1:1989, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013

