

Crimp Fittings

Press-armaturen


Embouts sertis

Raccordi a graffare

Racores para presión

FLA (3000 psi)

Split Flange Code 61, 45° Elbow
 Flansch-Code 61, 45° Krümmer
 Bride code 61, coudé 45°
 Flangia codice 61 a 45°
 Brida-código 61 acodado a 45°



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G8FLA8	1S8FLA8	1A8FLA8		1/2"			-8	79,1	49,4	19,8	9,6			30,2
1G12FLA8	1S12FLA8	1A12FLA8		3/4"			-8	92,5	62,8	25,4	9,6			38,1
1G12FLA12	1S12FLA12	1A12FLA12		3/4"			-12	94,8	64,6	25,4	15,5			38,1
1G16FLA12	1S16FLA12	1A16FLA12		1"			-12	105,7	75,5	26,9	15,5			44,4
1G12FLA16	1S12FLA16	1A12FLA16		3/4"			-16	98,9	64,5	25,4	20,7			38,1
1G16FLA16	1S16FLA16	1A16FLA16		1"			-16	110,5	76,0	26,9	20,7			44,4
1G20FLA16	1S20FLA16	1A20FLA16		1 1/4"			-16	122,1	87,6	29,2	20,7			50,8
1G16FLA20	1S16FLA20	1AP16FLA20*		1"			-20	121,8	77,8	26,9	26,6			44,4
		1AT16FLA20**		1"			-20	121,8	77,8	26,9	26,6			44,5
1G20FLA20	1S20FLA20	1AP20FLA20*		1 1/4"			-20	133,5	89,5	29,2	26,6			50,8
		1AT20FLA20**		1 1/4"			-20	133,6	89,4	29,2	26,6			50,8
1G24FLA20	1S24FLA20	1AP24FLA20*		1 1/2"			-20	150,8	106,8	35,8	26,6			60,3
		1AT24FLA20**		1 1/2"			-20	150,8	106,8	35,8	26,6			60,3
1G24FLA24	1S24FLA24	1A24FLA24		1 1/2"			-24	154,2	107,9	35,8	32,0			60,3
1G32FLA24	1S32FLA24	1A32FLA24		2"			-24	186,2	139,9	50,8	32,0			71,4
1G32FLA32	1S32FLA32	1A32FLA32		2"			-32	190,3	138,1	50,8	44,4			71,4

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

Specification subject to change without notice