


# EBC006



## Splitter box

ZDO6H057MSS0000-00STAK120MSS




Application	
Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes
Electrical data	
Operating voltage [V]	10...30 DC; ("supply class 2" to cULus)
Max. current load per module/slot [A]	4
Max. current load total [A]	12
Outputs	
Electrical design	PNP

# EBC006



## Splitter box

ZDO6H057MSS0000-00STAK120MSS

Operating conditions		
Ambient temperature [°C]		-25...80
Protection		IP 67; ("enclosure type 1" according to cULus)
Mechanical data		
Weight [g]		240.5
Dimensions [mm]		33 x 60 x 125
Materials		PA
Number of ports splitter box		6
Connector type		M12
Displays / operating elements		
Display	switching status	6 x LED, yellow
	operation	1 x LED, green
Accessories		
Accessories (supplied)		Protective caps: 2 labels: 6
Remarks		
Pack quantity		1 pcs.
Electrical connection - Connection		
Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm		
		


# EBC006



## Splitter box

ZDO6H057MSS0000-00STAK120MSS

### Connection



### Electrical connection - slot

Connector: 6 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

