



**T COUPLER SLIMLINE M12 MALE / M12 FEMALE 0°**

Male straight to female straight, fixed  
T-coupler (Slimline) M12 - M12  
4-pole

[Link to Product](#)**Illustration**



Product may differ from Image

### Approvals



### Form

41165

### Technical Data

Operating voltage	60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

### General data

Temperature range	-25...+85 °C
-------------------	--------------

### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1