



### Model Number

NJ4-12GM40-E2-5M

### Features

- Comfort series
- 4 mm non-flush

### Accessories

BF 12

Mounting flange, 12 mm

## Technical Data

### General specifications

Switching element function		PNP	NO
Rated operating distance	$s_n$	4 mm	
Installation		non-flush	
Output polarity		DC	
Assured operating distance	$s_a$	0 ... 3.24 mm	
Actual operating distance	$s_r$	3.6 ... 4.4 mm typ.	
Reduction factor $r_{AI}$		0.37	
Reduction factor $r_{Cu}$		0.36	
Reduction factor $r_{304}$		0.74	

### Nominal ratings

Operating voltage	$U_B$	10 ... 60 V
Switching frequency	$f$	0 ... 2000 Hz
Hysteresis	$H$	1 ... 10 typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	$U_d$	$\leq 3$ V
Voltage drop at $I_L$		
Voltage drop $I_L = 100$ mA, switching element on $U_d$		1.2 ... 2.5 V
Operating current	$I_L$	0 ... 200 mA
Off-state current	$I_r$	$\leq 0.5$ mA
No-load supply current	$I_0$	$\leq 9$ mA
Time delay before availability	$t_v$	$\leq 20$ ms
Switching state indicator		LED, yellow

### Functional safety related parameters

MTTF <sub>d</sub>	750 a
Mission Time ( $T_M$ )	20 a
Diagnostic Coverage (DC)	0 %

### Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
Storage temperature	-40 ... 85 °C (-40 ... 185 °F)

### Mechanical specifications

Connection type	cable PUR, 5 m
Core cross-section	0.34 mm <sup>2</sup>
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	PBT
Degree of protection	IP67

### General information

Scope of delivery	2 self locking nuts in scope of delivery
-------------------	--


### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Certified by China Compulsory Certification (CCC)

## Dimensions



Electrical Connection



Release date: 2016-08-04 16:05 Date of issue: 2016-08-04 282948\_eng.xml