

ACCESSORY FOR 3KF ALL FR SIZES ELECTR FUSE
MONITORING



Model	
Product brand name	SENTRON
Insulation voltage / rated value	250 V
Surge voltage resistance / rated value	4 kV
Protection class IP	IP20
Operating voltage / at AC / rated value / minimum	230 V
Number of CO contacts / of auxiliary contacts / instantaneous contact	1
Number of NC contacts / for auxiliary contacts / instantaneous contact	0
Number of NO contacts / for auxiliary contacts / instantaneous contact	0
Operating current / of auxiliary contacts / at AC-15 / at 230 V	1.5 A
Color / of the actuating element	gray
Product component / Phase failure monitoring	No
Connectable conductor cross-section / for auxiliary contacts / single or multi-stranded	
• minimum	0.2 mm ²
• maximum	2.5 mm ²

Tightening torque / with screw-type terminals	
<ul style="list-style-type: none"> • minimum • maximum 	<p>0.5 N·m</p> <p>1.2 N·m</p>
Net weight	150 g
Ambient temperature	
<ul style="list-style-type: none"> • during operation / minimum • during operation / maximum • during storage / minimum • during storage / maximum 	<p>-20 °C</p> <p>65 °C</p> <p>-20 °C</p> <p>80 °C</p>
Equipment marking	
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 	<p>Q</p> <p>Q</p>

Declaration of Conformity	other
----------------------------------	--------------



[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3KF9010-1AA00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3KF9010-1AA00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3KF9010-1AA00

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



