

Monitor film 19" widescreen for Flat Panel, cuttable for other sizes, additional information, amount and content: see technical data



Figure similar

General information	
Product type designation	Monitor film for 19" widescreen
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Standards, approvals, certificates	
CE mark	Yes
RoHS conformity	Yes
Ambient conditions	
Suited for indoor use	Yes
Suited for outdoor use	No
Ambient temperature during operation	
• min.	-20 °C
• max.	80 °C
Ambient temperature during storage/transportation	
• min.	15 °C

• max.	30 °C
Relative humidity	
• Operation, max.	50 %
Mechanics/material	
Material	
• Plastic	Yes; Non-reflecting, matte, can be removed without residue, hard-coated, dirt-repellant
Enclosure material (front)	
• PET	Scratching hardness 2H, adhesive force 0.011 N/25 mm Yes; Polyester with functional hard layer, silicone adhesive
Dimensions	
Width	409 mm
Height	231 mm
Thickness	0.225 mm
Weights	
Weight without packaging	34 g; Per unit
Scope of supply	
Delivery quantity in pieces	5; Units per set
Other	
printable with laser printer	No
Merchandise	Yes; URM55 reflection shield, matte
Manufacturer name	Bedifol GmbH
Manufacturer's address	Byk-Gulden-Straße 2 // F22, 78467 Constance, Germany
Target devices	For 19" widescreen flat panels, can also be cut to size for smaller, glass front displays, not suitable for membrane fronts
Usable in the following products	
• Product 1	6AV7863-3MA20-0AAx
• Product 2	6AV7863-3MA20-0AA0
last modified:	10/13/2017