

Lengte x breedte mm		300 x 200		400 x 300							
Hoogte mm		75	145	50	75	120	145	175	210	270	320
Inhoud liter		2,7	5,5	4,5	7	10	13	15	19	24	29
VE = stuks		8	8	4	4	4	4	4	4	4	4
Draagverm. / belasting kg		-	15 / 250	10 / 250	12,5 / 250	15 / 250	20 / 250	20 / 250	25 / 250	25 / 250	30 / 250
Wanden en bodem opengewerkt	blauw	-	203976	531618	531624	203993	204008	204025	204041	204058	204074
	rood	-	203977	531620	531625	203994	204009	204026	204042	204059	204075
	groen	-	203978	531621	531626	203995	204010	204027	204043	204060	204076
	geel	-	203979	531622	531627	203996	204012	204028	204045	204061	204078
	grijs	-	203980	531623	531628	203997	204013	204029	204046	204062	204079
Prijs per VE		---	---	---	---	---	---	---	---	---	---
Draagverm. / belasting kg		20 / 300	15 / 300	17,5 / 300	20 / 300	25 / 300	25 / 300	30 / 300	30 / 300	30 / 300	35 / 300
Wanden opengewerkt Bodem gesloten	blauw	-	203982	531629	531634	203998	204014	204030	204047	204063	204080
	rood	-	203983	531630	531635	203999	204015	204031	204048	204064	204081
	groen	-	203984	531631	531636	204000	204016	204032	204049	204065	204082
	geel	-	203985	531632	531637	204001	204017	204034	204050	204067	204083
	grijs	-	203986	531633	531638	204002	204018	204035	204051	204068	204084
Prijs per VE		---	---	---	---	---	---	---	---	---	---
Draagverm. / belasting kg		25 / 500	25 / 500	20 / 500	25 / 500	30 / 500	35 / 500	35 / 500	40 / 500	40 / 500	45 / 500
Wanden en bodem gesloten	blauw	203971	203987	531639	531645	204003	204019	204036	204052	204069	204085
	rood	203972	203988	531640	531646	204004	204020	204037	204053	204070	204086
	groen	203973	203989	531642	531647	204005	204021	204038	204054	204071	204087
	geel	203974	203990	531643	531648	204006	204022	204039	204056	204072	204089
	grijs	203975	203991	531644	531649	204007	204024	204040	204057	204073	204090
Prijs per VE		---	---	---	---	---	---	---	---	---	---
Direct meebestellen											
Sluitdeksel, zwart		508883	508883	508885	508885	508885	508885	508885	508885	508885	508885
VE = 4 stuks		---	---	---	---	---	---	---	---	---	---
Oplegdeksel, zwart		508892	508892	508894	508894	508894	508894	508894	508894	508894	508894
VE = 4 stuks		---	---	---	---	---	---	---	---	---	---

Lengte x breedte mm		600 x 400									
Hoogte mm		50	75	120	145	175	210	270	320		
Inhoud liter		9,5	14,5	22	26	33	40	51	61		
VE = stuks		2	2	2	2	2	2	2	2		
Draagverm. / belasting kg		15 / 250	20 / 250	25 / 300	30 / 300	30 / 300	35 / 300	35 / 300	45 / 300		
Wanden en bodem opengewerkt	blauw	531650	531656	204109	204126	204142	204159	204175	204191		
	rood	531651	531657	204110	204127	204143	204160	204176	204192		
	groen	531653	531658	204111	204128	204144	204161	204177	204193		
	geel	531654	531659	204112	204129	204145	204162	204178	204194		
	grijs	531655	531660	204114	204130	204147	204163	204180	204195		
Prijs per VE		---	---	---	---	---	---	---	---		
Draagverm. / belasting kg		20 / 300	25 / 300	30 / 400	35 / 400	35 / 400	40 / 400	40 / 400	50 / 400		
Wanden opengewerkt Bodem gesloten	blauw	531661	531667	204115	204131	204148	204164	204181	204196		
	rood	531662	531668	204116	204132	204149	204165	204182	204197		
	groen	531664	531669	204117	204133	204150	204166	204183	204198		
	geel	531665	531670	204118	204134	204151	204167	204184	204199		
	grijs	531666	531671	204119	204136	204152	204169	204185	204200		
Prijs per VE		---	---	---	---	---	---	---	---		
Draagverm. / belasting kg		30 / 500	35 / 500	40 / 600	45 / 600	45 / 600	50 / 600	50 / 600	60 / 600		
Wanden en bodem gesloten	blauw	531672	531678	204120	204137	204153	204170	204186	204201		
	rood	531673	531679	204121	204138	204154	204171	204187	204202		
	groen	531675	531680	204122	204139	204155	204172	204188	204203		
	geel	531676	531681	204123	204140	204156	204173	204189	204205		
	grijs	531677	531682	204125	204141	204158	204174	204190	204206		
Prijs per VE		---	---	---	---	---	---	---	---		
Direct meebestellen											
Sluitdeksel, zwart		508902	508902	508902	508902	508902	508902	508902	508902		
VE = 4 stuks		---	---	---	---	---	---	---	---		
Oplegdeksel, zwart		508908	508908	508908	508908	508908	508908	508908	508908		
VE = 4 stuks		---	---	---	---	---	---	---	---		



Bak

Met ingreepopening aan kopzijde en grootvolumebak

Lengte x breedte mm		600 x 400 (kopzijde open)		800 x 600 (grote container)	
Hoogte mm		270	320	210	320
Inhoud liter		51	61	78	127
VE = stuks		2	2	2	1
Draagverm. / belasting kg		40 / 350	40 / 350	70 / 600	110 / 600
Wanden opengewerkt Bodem gesloten	blauw	204207	204213	204220	204231
	rood	204208	204214	204221	204232
	groen	-	-	204222	204233
	geel	-	-	204223	204234
	grijs	204209	204216	204224	204235
Prijs per VE		---	---	---	---
Draagverm. / belasting kg		50 / 500	50 / 500	80 / 800	125 / 800
Wanden en bodem gesloten	blauw	204210	204217	204225	204236
	rood	204211	204218	204227	204238
	groen	-	-	204228	204239
	geel	-	-	204229	204240
	grijs	204212	204219	204230	204241
Prijs per VE		---	---	---	---
Direct meebestellen					
Sluitdeksel, zwart		508902	508902	-	-
VE = 4 stuks		---	---	---	---
Oplegdeksel, zwart		508908	508908	508919	508919
VE = 4 stuks		---	---	---	---

Ingreepopening aan kopzijde, 265 x 172 mm