

PT100 probe, general purpose, 2 m



The SE011 is a low-cost platinum resistance thermometer probe that can be used in non-specialized temperature measurements in immersion, air and insertion applications.

SE011 PT100 probe specifications	
Temperature range	-30 to +350 °C
Accuracy	±0.15 °C @ 0 °C Class A
Dimensions	
Length	150 mm
Diameter	6 mm
Cable	2 m
Material	Stainless steel probe, PVC cable
Handle	No
Connector	4-pin mini-DIN