Silicone Endstop Buffers • truncated cone form

25151.0032

Product Description

Because of the high material purity, this version is suitable for all types of application which have demanding hygienic requirements (e.g. foodstuffs industry).
To be used as an elastic end-stop, bearing foot etc.
Endstop buffers made from silicone rubber have a wider temperature range for use than rubber endstop buffers.
The hardness is 55 ±5° shore A. Further shore hardnesses (40 ±5° shore A and 70 ±5° shore A) on request.

Material

Support washer
- Stainless steel 1.4301

Threaded bushing
- Stainless steel 1.4301

Body
- Silicone rubber

More information

Further products

- Rubber Endstop Buffers, truncated cone form

Drawing



picture 1



picture 2

Order information

Dimensions						Spring rate R ~	Load capacity max.	Spring range ~				Art. No.
d_1	d_2	d_3	l_1	s	t				min.	max.		
[mm]						[N/mm]	[N]	[mm]	[°C]		[g]	
with female thread – picture 1												
32	**M8**	21	26	2	8	117	760	6.5	-30	200	23	25151.0032

Compliance

RoHS-compliant
Compliant with Directive 2011/65/EU [RoHS].

Does not contain SVHC substances
No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 25.06.2025.

SCIP-code
N/A

Does not contain Proposition 65 substances
No Proposition 65 substances included.
https://www.P65Warnings.ca.gov/

Free from Conflict Minerals
This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

POP-compliant
Contains no persistent organic pollutants – Stockholm Convention [POP] as of September 2025.

PFAS-compliant
Contains no per- and polyfluoroalkyl substances (PFAS).

TSCA-compliant
Agent concentration in this product does not exceed the specified threshold.