

## 15" RackMount Console

### An Ideal Solution for Complete KVM Management

LevelOne announces the release of KVM-0115 and KVM-0117 KVM RackMount Console that incorporates a display with keyboard and trackball to manage the remote servers.

### Multiple Input Interfaces

The LevelOne KVM-0115 and KVM-0117 provides the most economical and convenient server management-solutions available in today's competitive network management markets.

Equipped with an integrated PS/2 and USB interface to control workstations through its integrated keyboard, touchpad and TFT display the KVM management switches provide full management access to server farms and other systems connected.

### Bright Active Matrix TFT Display

The KVM-0115 and KVM-0117 KVM RackMount Console are available with either a 15 inch or 17 inch bright active matrix TFT display. With high resolutions display of up to 1024x768 on the 15 inch KVM-0115 and 1280x1024 on the 17 inch KVM-0117 LCD Drawers, system and server status can easily be monitored and managed from the TFT display.

### Quick and Easy Installation

The LevelOne KVM-0115 and KVM-0117 also feature a unique 1U rack-mountable dual-rail design for easy installation and quick access in server control rooms or in a remotely controlled location.



**KVM-0115**

### Related Products



**KVM-0820**

8-Port KVM Switch w/OSD for USB and PS/2



**KVM-0830**

8-Port Combo KVM

## Key Features

- **Bright Active Matrix TFT Display**
- **OSD function for LCD display**
- **Panel Protected by Tempered Glass**
- **15 pins high density connector**
- **15 Language keyboard format and easy glide touchpad**
- **Durable Keyboards (touchpad or trackball)**
- **Support PS/2 and USB Console Interface**
- **Support DVI Interface**

## Technical Specification

Model Name	KVM-0115	KVM-0117
Display Size	15"	17"
Number of Ports	1	1
PC Interface	2 x PS/2 1 x USB 1 x DVI	
Panel Type	Active Matrix TFT LCD	
Resolution Capabilities	Max Resolution up to 1024 x 768 (XGA)	Max Resolution up to 1280 x 1024 (SXGA)
Pixel Pitch	0.297mm x 0.297mm	0.264mm x 0.264mm
Active Display Area	15 inches diagonal	17 inches diagonal
Viewing Angle	R-L 130° (Right-Left view) U-P 100° (Up-Down view)	R-L 60°~70° (Right-Left view) U-P 45°~60° (Up-Down view)
Contrast Ratio	400 : 1	450 : 1
Brightness	White 250 cd/m <sup>2</sup> (Centre 1 point Typ)	
Back Light	Dual Lamps for Back Light	Four Lamps for Back Light
Colors Supported	16M colors (6-bit with FRC)	
Response Time	Rising Time 5ms Decay Time 11ms	Rising Time 2ms Decay Time 14ms
Operating System	DoS, Windows (3.1, 9x, 2000, NT4, ME, XP, 2003 Server), Linux, Novell 2.12-6, HP UX, SUN	
Multi-Platform	Support PS/2, USB and SUN	
Keyboard Mouse	106 Keys ps/2 keyboard with easy glide touchpad	
Sync	45~80KHz	
Input Connector	DB-15, 3-in-one connector	
System Cable	VGA + 2 x PS/2 Cable	
Power Source	100~240 VAC input	
Power Consumption	Total 16W, 10.41W for Panel	Total 25W, 19.05W for Panel
Temperature	Operating: 0°C ~50°C / 32°F ~ 122°F Storage: 20°C ~60°C / -4°F ~ 140°F	
Humidity	Operating: 10% ~ 90% (non-condensing)	
Dimension	447.5 x 482 x 44mm/ 17.6 x 19.0 x 1.7in	447.5 x 482 x 44mm/ 17.6 x 19.0 x 1.7in
Net Weight	11.8Kg/ 26.0Lb	13.0Kg/ 28.7Lb
Gross Weight	15.8Kg/ 34.8 Lb	17Kg/ 37.5 Lb
Chassis Construction	Heavy duty steel material	
Certification	CE, FCC	

## Ordering Information

- KVM-0115DE: KVM 15" RackMount Console with DE Keyboard
- KVM-0115US: KVM 15" RackMount Console with US Keyboard
- KVM-0117DE: KVM 17" RackMount Console with DE Keyboard
- KVM-0117US: KVM 17" RackMount Console with US Keyboard