

Product information

87 02 180 T

KNIPEX Cobra®

High-Tech Water Pump Pliers

DIN ISO 8976



- Pliers with tether attachment point for mounting a fall protection system
- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

| | |
|-----------------|---|
| Article No. | 87 02 180 T |
| EAN | 4003773080145 |
| Pliers | grey atramentized |
| Head | polished |
| Handles | with multi-component grips, with integrated tether attachment point for a tool tether |
| Weight | 200 g |
| Dimensions | 180 x 54 x 20 mm |
| Standard | DIN ISO 8976 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|---------------------------------|---------|
| Adjustment positions | 18 |
| Kapazität für Rohre (Zoll) | Ø 1 1/2 |
| Capacities for nuts | 36 mm |
| Capacities for pipes (diameter) | Ø 42 mm |
| Drop Protection System | yes |

technical change and errors excepted



