

# Models...

## ATB 5 & 10

N.m or lbf.in versions come with either a 8mm spigot or a 9x12 carrier rectangular fitting

Want to know how to use this tool?



Watch our video



Details of Accessories... see pages 67 & 69 or visit [www.torqueleader.com](http://www.torqueleader.com)



Order Code: **080015**

Order now... call our Sales Hotline +44 (0) 1483 894 476

Order Code	Model	ISO	←———— Calibrated Range ———→			Drive	k mm	kg	Accuracy	ISO 6789 Class	
			SI	Imperial	SI						
050500	ATB 5	1-5 N.m	0.025 N.m	-	-	⊗	220	0.29	+/- 6%	2A	✓
050505	ATB 5	-	-	10-45 lbf.in	0.25 lbf.in	⊗	220	0.29	+/- 6%	2A	✓
050507	ATB 5 G	1-5 N.m	0.025 N.m	-	-	⊗ <sub>12</sub>	230	0.29	+/- 6%	2A	✓
050512	ATB 5 G	-	-	10-45 lbf.in	0.25 lbf.in	⊗ <sub>12</sub>	230	0.29	+/- 6%	2A	✓
050550	ATB 10	2-10 N.m	0.05 N.m	-	-	⊗	220	0.30	+/- 6%	2A	✓
050555	ATB 10	-	-	20-90 lbf.in	0.5 lbf.in	⊗	220	0.30	+/- 6%	2A	✓
050557	ATB 10 G	2-10 N.m	0.05 N.m	-	-	⊗ <sub>12</sub>	230	0.30	+/- 6%	2A	✓
050562	ATB 10 G	-	-	20-90 lbf.in	0.5 lbf.in	⊗ <sub>12</sub>	230	0.30	+/- 6%	2A	✓