

FW22 - Steelite Metatarsal Boot S3 HRO M

Collection: Steelite™ Work

Range: Footwear

Material Upper: Split Leather

Material Outsole: PU/Rubber

Outer Carton: 12

Product information

Leather upper, steel toecap and midsole with tough steel metatarsal cover offers supreme protection and comfort for the wearer. Heat resistant outsole with the highest slip resistance grade makes this boot suitable for wear in all weather conditions.

Steelite™ Work

Fully Compliant with all current standards, ideal for industrial wear with a strong and flexible construction.

Footwear

Innovation, design, styling and quality components define the Portwest foot protection collection.

Standards

ASTM F2413-18

EN ISO 20345 S3



Features

- Protective leather flap to guard against sparks
- Flame resistant stitching
- Integrated superior metatarsal protection for heavy duty industries
- Padded collar for added comfort
- Slip, fuel and oil resistant rubber outsole
- Heat resistant outsole 300°C
- Protective steel toecap
- Pierce resistant steel midsole
- Anti-static footwear
- Energy Absorbing Seat Region
- SRC - Slip resistant outsole to prevent slips and trips on ceramic and steel surfaces



PRODUCT SPECIFICATION & TECHNICAL DATA

FW22 - Steelite Metatarsal Boot S3 HRO M
Commodity Code: 6403400000

Test House

Cert No: LEC FI00349270

CARTON DIMENSIONS/WEIGHT

Item	Colour	Len	Wid	Hgt	Weight (Kg)	Cubic (m ³)	EAN13	DUN14
FW22BKR38	Black	65.0	49.5	36.0	1.6010	0.1158	5036108255382	15036108743572
FW22BKR39	Black	65.0	49.5	36.0	1.6350	0.1158	5036108255399	15036108743589
FW22BKR40	Black	65.0	49.5	36.0	1.6820	0.1158	5036108255405	15036108743596
FW22BKR41	Black	65.0	49.5	36.0	1.7490	0.1158	5036108255412	15036108743602
FW22BKR42	Black	65.0	49.5	36.0	1.8190	0.1158	5036108255429	15036108743619
FW22BKR43	Black	65.0	49.5	36.0	1.9010	0.1158	5036108255436	15036108743626
FW22BKR44	Black	70.0	53.5	39.0	1.9670	0.1461	5036108255443	15036108743633
FW22BKR45	Black	70.0	53.5	39.0	1.9910	0.1461	5036108255450	15036108743640
FW22BKR46	Black	70.0	53.5	39.0	2.0290	0.1461	5036108255467	15036108743657
FW22BKR47	Black	70.0	53.5	39.0	2.0510	0.1461	5036108255474	15036108743664
FW22BKR48	Black	70.0	54.0	39.0	2.0710	0.1474	5036108310098	15036108798695