

## Radial tool holder shape B3 overhead right-hand, short

**ORION**<sup>®</sup>

### Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm<sup>2</sup>
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground

<b>Art. no.</b>	<b>22778 062</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	22778062
<b>VDI mount diameter</b>	25 mm
<b>Form</b>	B3 R overhead
<b>Height</b>	16 mm
<b>Width</b>	55 mm
<b>Holder width</b>	30 mm
<b>Width 2</b>	7 mm
<b>Height 2</b>	25 mm
<b>Height 3</b>	30 mm
<b>Holder support length</b>	16 mm
<b>Length</b>	30 mm
<b>DIN</b>	69880-1
<b>Gross Weight</b>	0.760 kg
<b>Product Group</b>	2AC



### EAN

4053625464722