


# Butt Splice Connectors

## Vinyl insulated



### SPECIFICATION:

Material	Copper
Surface material	Tin-plated
Max temperature	+105 °C
Max. Voltage	600 V
Adhesive Inside	Yes



### PRODUCT RANGE:

Article Nr.	Cross-section	AWG	Max. Current	Colour	D	L	d	t	E	C	t1
RND 465-00573	0.5...1.5 mm <sup>2</sup>	22-16 AWG	19 A	Red	5.8 mm	24 mm	4.3 mm	0.75 mm	15 mm	4.9 mm	0.8 mm
RND 465-00574	1.5...2.5 mm <sup>2</sup>	16-14 AWG	27 A	Blue	6.2 mm	24 mm	4.5 mm	0.8 mm	15 mm	5.7 mm	0.8 mm
RND 465-00575	4...6 mm <sup>2</sup>	12-10 AWG	48 A	Yellow	8.1 mm	27 mm	6.5 mm	1 mm	15 mm	7.1 mm	0.8 mm