


SERIES 142 ERSADUR LONGLIFE SOLDERING TIPS

■ i-CON TRACE with i-TOOL TRACE soldering iron




0142SDLF04L/SB

pencil point, bent, extended,
0.4 mm ϕ




0142SDLF06L/SB

pencil point, bent,
extended, 0.6 mm ϕ




0142SDLF08L/SB

pencil point, bent,
extended, 0.8 mm ϕ




0142ADLF13/SB

angled face, 1.3 mm ϕ




0142ADLF15/SB

angled face, 1.5 mm ϕ




0142ADLF22/SB

angled face, 2.2 mm ϕ




0142ADLF32/SB

angled face, 3.2 mm ϕ




0142ADLF40/SB

angled face, 4.0 mm ϕ




0142ZDLF100/SB

WICK-TIP, 10.0 mm




0142ZDLF150/SB

WICK-TIP, 15.0 mm




0142ZDLF200/SB

WICK-TIP, 20.0 mm




0142BDLF20/SB

PLCC blade




0142WDLF16/SB

PowerWell with concave portion,
1.6 mm ϕ




0142WDLF23/SB

PowerWell with concave portion,
2.3 mm ϕ



0142WDLF35/SB

PowerWell with concave portion,
3.5 mm ϕ



Dimensions without pre-tinning