

# ExStik<sup>®</sup> Waterproof Refillable pH Meter

**Features flat surface electrode, RENEW and CALibration alerts, memory, and bargraph**  
Indicator tells you it's time to replace your electrode and eliminates guesswork

## Features:

- ✓ Refillable pH electrode is easily serviced. Fresh reference solution maintains high accuracy. Eliminates concern with shelf life.
- ✓ Flat Surface Electrode measures pH in liquids, semi-solids, and solids. No more electrode breakage or clogged junctions.
- ✓ CAL alerts tells you it's time to recalibrate. Ensures accuracy.
- ✓ Memory records and recalls 15 sequentially tagged readings. Allows detection of changes over time.
- Analog bargraph displayed on LCD. Shows trends in acidity or alkalinity.
- 1, 2 or 3 point calibration automatically recognizes buffer solutions. Order pH buffers separately.
- Automatic Temperature Compensation
- Simultaneous display of pH and Temperature
- Waterproof to IP57 standard
- Display indicates when the reading is stabilized
- Data Hold, Auto power off and low battery indication
- Waterproof design floats in water and protects the meter in wet environment
- Interchangeable probes available for Chlorine & ORP
- Optional weighted base (EX006) holds plastic cup and ExStik<sup>®</sup> meter
- Complete with refillable flat surface pH electrode, 1.5mL bottle KCl, 2 reference junctions, 2 removal tools, protective sensor cap, sample cup with cap, four 3V CR-2032 button batteries, and 48" (1.2m) neckstrap. **Order pH buffers separately**

## Ordering Information:

PH110 .....Waterproof Refillable ExStik<sup>®</sup> pH Meter  
 PH115 .....Spare Refillable pH ExStik<sup>®</sup> Electrode Module  
 PH113 .....Reference Refill Solution Kit for PH110  
 EX006.....Weighted base with 5 solution cups  
 PH103 .....Tripack buffers (6ea - 4, 7, 10pH & 2 Rinse solutions)  
 PH105 .....Spare pH ExStik<sup>®</sup> Electrode Module  
 EX007.....Spare sample solution cups (24pk)  
 CA903 .....Carrying case for ExStik<sup>™</sup> kit  
 RE305.....Spare Probe, ORP  
 CL205.....Spare Probe, Chlorine  
 EX010.....Extension Cable, 3ft (1 Meter) with probe weight for ExStik  
 EX050 .....Extension Cable, 16ft (5 Meter) with probe weight for ExStik  
 PH115 .....Spare Probe, pH, Refillable Reference  
 PH4-P.....pH 4 Buffer Solution (2 Bottles, 1 Pint (475 mL) Each)  
 PH7-P.....pH 7 Buffer Solution (2 Bottles, 1 Pint (475 mL) Each)  
 PH10-P.....pH 10 Buffer Solution (2 Bottles, 1 Pint (475 mL) Each)  
 CA895 .....Carrying Case, Small with Belt Loop  
 EX800.....ExStik 3-in-1 Kit (Chlorine, pH, Temp)  
 EX900.....ExStik 4-in-1 Kit (Chlorine, pH, ORP, Temp)  
 D0610 .....ExStik DO/pH/Conductivity Kit



**Model PH113 Reference Refill Solution Kit includes:**

1.5mL bottle KCl,  
2 reference junctions and  
2 removal tools.



Specifications	
pH	0.00 to 14.00pH
Temperature	23 to 194°F (-5 to 90°C)
Resolution	0.01pH, 0.1°
Accuracy	±0.01pH, ±1.8°F/±1°C
Power	four LR44 button batteries
Dimensions	1.4 x 6.8 x 1.6" (35.6 x 172.7 x 40.6mm)
Weight	3.8oz (110g)

