



ELECTRONIC HOOK SWITCH CONTROL FOR AVAYA PHONES.

The Jabra LINK™ 14201-19 enables remote Electronic Hook Switch Control (EHS) with Jabra wireless headsets and a wide range of Avaya phones.

This means that users can hear ring tones, answer and end calls, adjust the volume or even mute the call up to 450 ft. away from their desks. The integration of handset and headset allows users to benefit from enhanced mobility and the ability to multitask while on a call. The wireless freedom improves work efficiency and ergonomics throughout the day.

HOW IT WORKS

The Jabra LINK 14201-19 is a plug-and-play solution that converts from the EHS standard used in Avaya phones to the DHSG or GN Netcom RHL standards used in Jabra headsets – and vice versa.

HANDSET-HEADSET COMPATIBILITY

The Jabra LINK 14201-19 is compatible with a wide range of Avaya phones. For more details see the technical specifications on page 2 or visit www.jabra.com/avaya.

THE JABRA LINK 14201-19 CAN BE USED WITH THESE JABRA HEADSETS



JABRA PRO™ 9400 SERIES

First wireless office headset with user-friendly touch screen for easy call control. Control calls to your desk, soft and mobile phone from the same headset!



JABRA GO™ 6470

First Bluetooth® office headset with user-friendly touch screen for easy call control. Control calls to your mobile, soft and desk phone from the same headset!



JABRA GN9350/JABRA GN9350e/JABRA GN9330e

Wireless dual-function headset that enables users to switch between PC-based VoIP and a desk phone.



JABRA GN9120/GN9125 SERIES

Award-winning wireless headset offering up to 300 ft range, three wearing styles, conference call capability and up to 8 hours talk time.

GN Netcom is a world leader in innovative headset solutions. GN Netcom develops, manufactures and markets its products under the Jabra brand name.

A BRAND BY







JABRA® IS A REGISTERED TRADEMARK OF GN NETCOM A/S

WWW.JABRA.COM



TECHNICAL SPECIFICATIONS

| SPECIFICATIONS | |
|----------------------------|--|
| JABRA LINK 14201-19 | Enables Electronic Hook Switch Control with Avaya and Jabra headsets |
| Item number | 14201-19 |
| Length of cables | 300 - 600 mm (118.1 - 236.2 inches) |
| Certification | CE, FCC, IC, NOM, C-Tick, China, Taiwan, Korea, Japan, Australia |
| Warranty | North America /APAC: One-year limited warranty. Europe: Two-year limited warranty |
| COMPATIBILITY | |
| Avaya Phones* | Avaya 2420 ver B on IP switch only, Avaya 2420 IP Ver Firmware> 4.0, Avaya 4610 & 4610SWFirmware> 1.8, Avaya 4620 & 4620SWFirmware> 1.8, Avaya 4621 & 4621SWFirmware> 1.8, Avaya 4622 & 4622SWFirmware> 1.8, Avaya 4625 & 4625SWFirmware> 1.8, Avaya 4630 & 4630SWFirmware> 1.8, Avaya 5420 Avaya 5620, Avaya 5621, Avaya 5625 |
| Jabra Headsets | Jabra PRO 9400 Series, Jabra GO 6470, Jabra GN9120/GN9125 EHS, Jabra GN9120/GN9125 DUO EHS, Jabra GN9350, Jabra GN9350e, Jabra GN9330 |
| EHS FEATURES | |
| Answer call | Yes |
| End call | Yes |
| Ring tone in headset | Yes |
| Volume control | Yes |
| Mute control | Yes |

| | Jabra PRO 9400 series Stay in touch around the office | Jabra GO 6470 Stay in touch wherever you are | Jabra GN9350e/ Jabra GN9330e EHS Superior sound and light weight comfort | Jabra GN9120/ Jabra GN9125 Award winning Scandinavian design |
|-------------------------|---|---|---|---|
| Connectivity |  (Mobile phone only for Jabra PRO 9470) |  |  (PC only for Jabra GN9350e) |  |
| Range | 150m** | Soft + deskphone: 100m** Mobile phone: 25m*** | 120m** | 150m** |
| Boom style | Jabra PRO 9470 - Midi Jabra PRO 9460 - Flex | Short | Midi | Flex |
| Touch screen | Yes | Yes | No | No |
| Auto set-up | Yes | Yes | No | No |
| Wideband sound | Yes | Yes | Yes (Jabra GN9350e with USB connection) | No |
| 2-mic Noise Blackout™ | Yes | Yes | No | No |
| Full hearing protection | Yes | Yes | Yes | No |
| Wearing styles in box | Headband + earhook + neckband (Neckband only for Jabra PRO 9470) | Headband + earhook**** | Headband + earhook + neckband (neckband only for Jabra GN9350e) | Headband + earhook |
| Conferencing | No | No | Yes/ No | Yes |
| EHS solution | Jabra LINK 14201-19 Jabra LINK 14201-20 | Jabra LINK 14201-19 Jabra LINK 14201-20 | Jabra LINK 14201-19 Jabra LINK 14201-20 | Jabra LINK 14201-19 Jabra LINK 14201-20 |

* A whole series of EHS adapters is available from GN Netcom that match the DHSG or GN Netcom RHL interfaces in a wide range of Avaya phones.

** Range varies according to the environment in which the headset is used

*** Range depends on the device with which the headset is connected

**** Neckband available as accessory