






Vnitřní průměr in / mm	Vnější průměr mm	Přetlak bar	Podtlak bar	Poloměr ohybu mm	Hmotnost kg/m	Rozměry skladem m	Číslo objednávky
2 / 50-51	58	0,480	0,170	33	0,240	5 10 15	531-0050-0000
2,36 / 60	68	0,405	0,145	38	0,340	5 10 15	531-0060-0000
2,5 / 63-65	73	0,370	0,130	40	0,360	5 10 15	531-0065-0000
- / 70	78	0,345	0,125	43	0,390	5 10 15	531-0070-0000
3 / 75-76	83	0,325	0,115	45	0,410	5 10 15	531-0075-0000
- / 80	88	0,305	0,110	48	0,440	5 10 15	531-0080-0000
3,5 / 89-90	98	0,270	0,095	53	0,490	5 10 15	531-0090-0000
4 / 100-102	108	0,245	0,055	58	0,520	5 10 15	531-0100-0000
- / 110	118	0,220	0,050	63	0,570	5 10 15	531-0110-0000
4,5 / 114-115	123	0,210	0,050	66	0,590	5 10 15	531-0115-0000
4,72 / 120	128	0,205	0,045	68	0,620	5 10 15	531-0120-0000
5 / 125-127	133	0,195	0,045	71	0,640	5 10 15	531-0125-0000
- / 130	138	0,185	0,040	73	0,680	5 10 15	531-0130-0000
5,5 / 140	148	0,175	0,040	78	0,720	5 10 15	531-0140-0000
6 / 150-152	158	0,160	0,035	83	0,770	5 10 15	531-0150-0000
6,3 / 160	168	0,150	0,035	88	0,820	5 10 15	531-0160-0000
7 / 178-180	188	0,135	0,030	98	0,920	5 10 15	531-0180-0000
8 / 200-203	208	0,120	0,025	108	1,040	5 10	531-0200-0000
- / 250	258	0,100	0,020	136	1,300	5 10	531-0250-0000
11 / 280	288	0,085	0,020	149	1,450	5 10 15	531-0280-0000
- / 300	309	0,080	0,015	159	1,730	5 10 15	531-0300-0000
- / 315	324	0,075	0,015	167,5	1,820	5 10 15	531-0315-0000
- / 350	359	0,070	0,015	185	2,010	5 10 15	531-0350-0000
- / 400	409	0,060	0,015	210	2,300	5 10 15	531-0400-0000





Vnitřní průměr in / mm	Vnější průměr mm	Přetlak bar	Podtlak bar	Poloměr ohybu mm	Hmotnost kg/m	Rozměry skladem m	Číslo objednávky
- / 40	47	1,020	0,335	27	0,260	5 10 15	532-0040-0000
1,75 / 44-45	52	0,910	0,300	30	0,290	5 10 15	532-0045-0000
2 / 50-51	58	0,820	0,220	33	0,360	5 10 15	532-0050-0000
- / 55	63	0,755	0,200	36	0,390	5 10 15	532-0055-0000
2,36 / 60	68	0,685	0,180	38	0,430	5 10 15	532-0060-0000
2,5 / 63-65	73	0,635	0,165	41	0,470	5 10 15	532-0065-0000
- / 70	78	0,590	0,155	43	0,500	5 10 15	532-0070-0000
3 / 75-76	83	0,550	0,145	46	0,530	5 10 15	532-0075-0000
- / 80	88	0,515	0,135	48	0,570	5 10 15	532-0080-0000
3,5 / 89-90	98	0,460	0,120	53	0,630	5 10 15	532-0090-0000
4 / 100-102	108	0,415	0,080	58	0,660	5 10 15	532-0100-0000
- / 110	118	0,375	0,070	63	0,730	5 10 15	532-0110-0000
4,72 / 120	128	0,345	0,065	68	0,790	5 10 15	532-0120-0000
5 / 125-127	133	0,335	0,065	71	0,820	5 10 15	532-0125-0000
- / 130	138	0,320	0,060	73	0,850	5 10 15	532-0130-0000
5,5 / 140	148	0,295	0,055	78	0,920	5 10 15	532-0140-0000
6 / 150-152	158	0,275	0,055	83	0,980	5 10 15	532-0150-0000
6,3 / 160	168	0,260	0,050	88	1,040	5 10 15	532-0160-0000
7 / 178-180	188	0,230	0,045	98	1,170	5 10 15	532-0180-0000
8 / 200-203	208	0,210	0,030	108	1,540	5 10 15	532-0200-0000
- / 225	233	0,185	0,025	121	1,750	5 10	532-0225-0000
- / 250	258	0,165	0,025	133	1,900	5 10 15	532-0250-0000
11 / 280	288	0,150	0,020	148	2,150	5 10	532-0280-0000
- / 300	309	0,140	0,020	159	2,530	5 10	532-0300-0000
- / 315	324	0,135	0,020	167	2,650	5 10	532-0315-0000
- / 350	359	0,120	0,020	184	2,950	5 10	532-0350-0000
- / 400	409	0,105	0,015	209	3,360	5 10	532-0400-0000





Vnitřní průměr in / mm	Vnější průměr mm	Přetlak bar	Podtlak bar	Poloměr ohybu mm	Hmotnost kg/m	Rozměry skladem m	Číslo objednávky
8 / 200-203	211	0,245	0,030	128	1,900	6 12	532-0200-2533
- / 225	236	0,215	0,025	143	2,100	6 12	532-0225-2533
- / 250	261	0,195	0,025	158	2,300	6 12	532-0250-2533
11 / 280	291	0,175	0,020	176	2,600	6 12	532-0280-2533
- / 300	311	0,160	0,020	188	2,800	6 12	532-0300-2533
- / 315	326	0,155	0,020	197	2,950	6 12	532-0315-2533
14 / 356	367	0,135	0,015	222	3,300	6 12	532-0356-2533
- / 400	411	0,120	0,015	248	3,700	6 12	532-0400-2533

