

24V Flexiprint

High bright (PLCC6)

Specifications










Voltage	24V
Current	3A
Wattage	14.4W/m
Number of LED's	300pcs
Length of Stripe	5m
Operating Temperature	-25°~+60°C
Storage Temperature	-40°~+80°C
Viewing Angle	110°
CE/RoHS compliant	




Benefits

Adhesive tape on backside
cuttable every ~100mm

Electrical and Optical Characteristics (Ta=25°C)

Part Number	Colour	Wavelength / CCT	Intensity lm (typ.)	EEC
FP3-A02D-500	 amber	605nm	540	E
FP3-B02D-500	 blue	472nm	290	E
FP3-G02D-500	 green	525nm	1200	D
FP3-H02D-500	 warm-white	2600-2800°K	5250	A
FP3-N02D-500	 warm-white	3000-3500°K	5250	A
FP3-R02D-500	 red	639nm	630	E
FP3-S02D-500	 natural-white	4000-5000°K	6000	A
FP3-W02D-500	 white	6000-7000°K	6000	A
FP3-Y02D-500	 yellow	590nm	540	E

Dimensions



Sloan_03_GK_LED-Modules_15B

Thickness: 2.1 mm

1. All dimensions are in millimetres
2. Tolerance is ± 0.25 mm unless otherwise specified
3. Specifications are subject to change without notice

Please also take note of our **General Information for Flexiprint and LED Modules**