

LINEARlight Colormix Flex

Flexible LED modules for professional and industrial applications



Areas of application

- Effect lighting in architecture
- Injection of light into displays and low-profile light guides
- Dynamic effects in public zones

Product benefits

- Uniform color changing
- Great design freedom thanks to flexibility and cuttability of module
- Simple mounting and connection
- Toolless connection with the optional CONNECTsystem
- Easy mounting on many smooth surfaces thanks to self-adhesive tape at the back

Product features

- Flexible and splittable LED strip with inline multichip RGB LEDs



Technical data

Electrical data

Product description	Nominal voltage	Nominal wattage	Reverse Voltage	Type of current
LF05CA2 -RGB3	24.00 V	72.00 W	25 V	DC
LF05CE -RGB1	24.00 V	39.0 W		DC

Product description	Voltage range
LF05CA2 -RGB3	23...25 V
LF05CE -RGB1	

Photometrical data

Product description	Luminous flux per meter	Luminous flux	Light color LED	Nominal dominant wavelength
LF05CA2 -RGB3	470 lm	1880 lm	RGB	625 / 525 / 465 nm
LF05CE -RGB1	180 lm	1080 lm	RGB	625 / 525 / 465 nm

Light technical data

Product description	Beam angle
LF05CA2 -RGB3	120 °
LF05CE -RGB1	120 °

LED module information

Product description	Number of LEDs per module	Number of LEDs per smallest unit
LF05CA2 -RGB3	200	5
LF05CE -RGB1	200	5


Dimensions & weight

Product description	Length	Length – smallest unit	Width	Height
LF05CA2 -RGB3	4000.0 mm	100.0 mm	8.0 mm	2.2 mm
LF05CE -RGB1	6000.0 mm ¹⁾	150.0 mm		


¹⁾ LED pitch 30 mm

Product line drawing

Product family datasheet



Product line drawing
LF05CA2 -RGB3



Product line drawing
LF05CE -RGB1

Temperatures

Product family datasheet

Product description	Temperature range in operation
LF05CA2 -RGB3	-30...75 °C ¹⁾
LF05CE -RGB1	

¹⁾ At the T_c point

Equipment / Accessories

- Simplified connection with optional matching CONNECTsystem
- Quick installation with optional SLIM TRACK System
- Perfectly matched to OPTOTRONIC 24 V Electronic Control Gears

Application advice

For more detailed application information and graphics please see product datasheet.








Sales and Technical Support

Sales and Technical Support www.osram.com







Country specific information

Product description	Product code	METEL-Code	SEG number	STK number	UK Org
LF05CA2 - RGB3	4008321851536	-	7500498	4030217	-
LF05CE-RGB1	4008321593375	OSRLF05CERGB1	8334072	4031372	-

Download Data

File	
	Product Datasheet LF05CA2 - Technical Datasheet
	Brochures FLEXIBLE LED MODULES
	Declarations of conformity EC-DoC LS LL05CA2
	Declarations of conformity EC-Man DoC LS LL05CA2
	Operating instructions LF05CA2 - User Manual
	Eulumdat 20121105 D012850 LF05CA2
	Eulumdat LF05CA2 D012849 LDT

Product family datasheet

	Eulumdat LF05CA2 D012848 LDT
	Product movie Spots LINEARlight Flex Quality long QTh264 3500kbit 1024x576 (E)
	Product movie Spots LINEARlight Flex Quality short QTh264 3500kbit 1024x576 (E)
	Product Datasheet LINEARlight Colormix Flex LF05C (data sheet)
	Declarations of conformity EC-DoC LF05CACE
	Declarations of conformity Manufacturers-DoC LF05CACE

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321851536	LF05CA2 -RGB3	Shipping carton box 8	205 mm x 195 mm x 241 mm	9.63 dm ³	1515.00 g
4008321593375	LF05CE -RGB1	Shipping carton box 8	205 mm x 195 mm x 241 mm	9.63 dm ³	1514.84 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.