



GeoLED

GEO LED 20W ROUND WHITE 4K

Order code **75323**

EAN 8002219722829

Technical specifications

Absorbed Power	20 W
Supply voltage type	AC
Nominal voltage (AC)	230 Vac
Ambient temperature (min)	-20 °C
Ambient temperature (max)	40 °C
Insulation class	II
CCT light tone	4000 K
Beam angle	120 °
Colour consistency	SDCM3
CRI color rendering	>80
Diameter	220 mm
Ballast	For constant current LED
Efficiency	82 lm/W
Frequency (max)	60 Hz
Frequency (min)	50 Hz
Power factor	0.55
Glow wire strength	850 °C - 30s.
MTBF driver	30000 h
Luminaire flux	1650 lm
Voltage supply range (max)	253 V
Voltage supply range (min)	207 V

Installation and applications

Environment	Secondary Areas
Application	Secondary Areas

Mechanical specifications

Height	70 mm
Weight	0.4 Kg
Colour housing	White
Protection grade IP	IP65
Protection grade IK	IK07

Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN IEC 60598-1:2021, EN 60598-2-1:1989, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013



