

PORTALÁMPARAS DE BAQUELITA BAQUELITE LAMP-HOLDER



PORTALÁMPARAS DE BAQUELITA / BAQUELITE LAMP-HOLDER



Código:	EM 09 079	
FORMA EXTERNA Y DIMENSIONES / EXTERNAL SHAPE AND DIMENSIONS	FORMA/SHAPE 161: Liso / <i>Plain</i> 162: Roscado / <i>Threaded</i> 163. Roscado con tope / <i>Threaded with stop ring.</i>	DIMENSIONES / DIMENSIONS Ø 39 x 54 mm Ø 40 x 58 mm Ø 40 X 54 mm
DIRECTIVA / DIRECTIVE	2014/35/UE REBT 2002 – Reglamento de Baja Tensión/ <i>Spanish Low Voltage Regulations</i>	
CARACTERÍSTICAS ELÉCTRICAS ELECTRICAL CHARACTERISTICS	Casquillo / Cap: Intensidad /Current: Tensión / Voltage: Frecuencia / Frequency:	E-27 4 A 250 V 50 / 60 Hz
MATERIAL	Baquelita / <i>Baquelite</i>	
COLOR / COLOUR	Blanco / <i>White</i> RAL9003	
MÉTODO DE FIJACIÓN / FIXING METHOD	Tuerca/ Nut Con tornillo antirotación / <i>with antirotating screw</i>	M10 x 1,0
TIPO DE BORNE / TERMINAL TYPE	Borne con tornillo / <i>Screw-type terminal</i>	
RESISTENCIA DE AISLAMIENTO / ISOLATION RESISTANCE	>4 M Ω	
RIGIDEZ DIELECTRICA / DIELECTRIC STRENGTH	1500 V	
NORMAS APLICADAS / APPLIED STANDARD	EN 60238	
Código:	EM 09 079	