




# 5x20mm PCB fuse carriers

## Product overview

- PCB mounting
- Kinked pin for PCB retention CFH02/W
- Transparent insulation cover CFH02H
- UL94-V0 cover
- 22.6mm pitch
- EN60127 and UL512
- approved

| PART NO. | TYPE         |
|----------|--------------|
| CFH02    | Straight pin |
| CFH02/W  | Kinked pin   |
| CFH02H   | Cover        |

| SPECIFICATION             |                                 |
|---------------------------|---------------------------------|
| Rating                    | 6.3A/ 250V                      |
| Contacts/resistance       | Tinned, nickel plated brass     |
| Moulding                  | UL94-V1 self extinguishing PPOM |
| Dielectric strength       | 3kV / 60 sec                    |
| Temperature               | -20° to 125°C                   |
| Operating power           | 1.6W                            |
| Recommended PCB hole size | 1.3mm                           |



# 5x20mm compact horizontal and vertical PCB mounting fuseholders

## Product overview

- Finger or screwdriver release, bayonet carrier
- Horizontal or vertical mounting
- Compact footprint 10mm pitch
- Anti solder wicking
- EN60127 and UL512
- approved



| SPECIFICATION             |                                  |
|---------------------------|----------------------------------|
| Rating                    | 10A/ 250V                        |
| Contacts/resistance       | Tinned nickel plated brass, <5mΩ |
| Moulding                  | UL94-V0 flame retardant PBT      |
| Dielectric strength       | 3kV / 60"                        |
| Power dissipation         | 2.5W                             |
| Recommended PCB hole size | 1.5mm                            |
| Insulation resistance     | 100MΩ                            |

| PART NO. | TYPE                |
|----------|---------------------|
| CFH06    | Vertical mounting   |
| CFH07    | Horizontal mounting |

