



Sample image

**Order symbol:** TA342912

**Product nbr:** 5814004

**Description:** Enclosure. ABS


**Remarks:** Opaque cover

**Including:** Base with PUR gasket and screws for mounting plate/DIN-rail. cover with polyamide cover screws and plastic hinges.

**EAN:** 6418074060761

**EI. number:**

- Finland: 3435690
- Denmark: B212035085
- Sweden: 5814004



Dimensions:	Height	Width	Depth
mm:	344	289	117
inch:	13.54	11.38	4.61

#### Accessories:

MP 3429	Mounting plate. for enclosures:
ARH 2328	DIN-35 Mounting rail. for enclosures: (260 x 35 x 1)
FP 10674	Mounting foot kit (2 pcs) incl. screws

**Materials:**

Material:	ABS
-----------	-----

Base colour:	
--------------	--

Cover colour:	
---------------	--

Gasket material:	
------------------	--

**Temperatures:**

Temperature °C (short term):	-40 ... 80
------------------------------	------------

Temperature °C (continuous):	
------------------------------	--

Temperature °F (short term):	-40 ... 175
------------------------------	-------------

Temperature °F (continuous):	-40 ... 140
------------------------------	-------------

DR 316

DIN-35 Mounting rail, for enclosures:  
(316 x 35 x 1)**Rating:**

Ingress protection (EN 60529):	IP65;
--------------------------------	-------

Impact Resistance (EN 62262):	IK07;
-------------------------------	-------

Electrical insulation:	Totally insulated
------------------------	-------------------

Halogen free (DIN/VDE 0472, Part 815):	1
--	---

UV resistance:	-
----------------	---

Flammability Rating:	UL 94 HB
----------------------	----------

Glow Wire Test (IEC 695-2-1) °C:	650 °C
----------------------------------	--------

NEMA Class	
------------	--

**Certificates:**

Certificate FI 40343	
----------------------	--